

# ACUROS® CQD® 640L USB3 eSWIR Camera

## **ACUROS-0640-USB3-004**

The ACUROS CQD L-Series extended SWIR (eSWIR) cameras feature large sensor area, low angular dependence and a long working distance for highly divergent emitters and collimated beams. Acuros cameras deliver high resolution, high dynamic range and very high detectivity imaging from 400 nm to 2000 nm. The L-Series cameras are designed for use exclusively in laser beam diagnostics, laser beam imaging and laser alignment applications by mitigating interference fringing sources.

#### **SPECIFICATIONS**

Table 1. ELECTRO-OPTICAL SPECIFICATIONS

Parameter	Value/Description	
Sensor	ACUROS CQD sensor	
Temperature Stabilization	Single-stage thermo-electric cooler	
Sensor Array Format	640 x 512	
Resolution	0.33 MP (megapixel)	
Spectral Band	400–2000 nm	
Array Size	9.6 mm x 7.7 mm, 12.3 mm diagonal	
Pixel Pitch	15 μm x 15 μm	
Max Frame Rate at Full Resolution	270 fps (8 bit), 180 fps (10, 12, 14 bit)	
Pixel Operability	99.9% typical, 99.75% min	
Bit Depth	8, 10, 12, 14 bit selectable	
Integration Type	Snapshot global shutter	
Trigger	External TTL	
Integration Time	100 μs to 4 s	
Dynamic Range	65 dB typical	
Windowing & Windowing Frame Rate	Array centered. Scales inversely to window size	
Laser Beam Fringeless Operation	Yes	
Binning Arrays	2 x 2, 4 x 4	
Non-uniformity Correction	2-point non-uniformity correction	
Temporal Dark Noise	80/70/65 e <sup>-</sup> typical	
Quantum Efficiency	See typical QE curve (Figure 4)	



#### **ORDERING INFORMATION**

Part Number
ACUROS-0640-USB3-004

#### **Features**

- · Large Sensor Size
- Short Working Distance for Highly Divergent Beams
- Low Angular Dependence
- Dynamic Range up to 70 dB
- Strong Linearity
- VGA Resolution
- TEC Cooling
- Low Noise
- GigE Vision
- Visible-SWIR

#### **Applications**

- Laser beam Diagnostics
- Laser Beam Imaging
- Laser Alignment

### ACUROS-0640-USB3-004

Table 2. ENVIRONMENTAL & POWER SPECIFICATIONS, TYPICAL PERFORMANCE

Parameter	Value/Description
Operating Case Temperature	-20 °C to +55 °C
Power Consumption	6.5-12 W depending on TEC settings
Power Supply Voltage	6-16 V dc
Regulatory Compliance	CE mark

#### **Table 3. MECHANICAL SPECIFICATIONS**

Parameter	Value/Description
Dimensions Excluding Lens	6.1 x 6.1 x 9.1 cm (C-mount)
Weight Excluding Lens	495 grams with (C-mount) adapter
Lens Mounts	Standard mount (C-mount). Inquire for other options.
Power Connector	Hirose 12-pin, HR10A-10R-12PB (71)
Trigger Connector	BNC

#### Table 4. SOFTWARE AND USER INTERFACE

Parameter	Value/Description
Software Development Kit	Windows GUI & Pleora eBUS SDK (Linux, Windows, macOS)
GenICam Compliance	Yes
Interface	USB3 Vision




Figure 1. F-mount and M-42 Lens Mounts



Figure 2. USB Vision Interface

### ACUROS-0640-USB3-004



1550 nm Laser image and corresponding line file (false color added post image)

Figure 3. ACUROS CQD SWIR Camera Image of Laser




Figure 4. Typical QE Performance

ACUROS, CQD and SWIR VISION SYSTEMS are registered trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries.

All other brand names and product names appearing in this document are registered trademarks or trademarks of their respective holders.





#### CMOD 90.89x61.00x61.00


CASE 810AF ISSUE A


**DATE 03 DEC 2024** 

















MILLIMETERS				
DIM	MIN	IN NOM MAX		
А	59.03	61.00	61.13	
D	90.69	90.89	91.09	
D1	86.19	86.39	86.59	
Е	59.03	61.00	61.13	
G1	30.37	30.50	30.63	
G2	30.37	30.50	30.63	
G3	30.49	30.61	30.74	
q	38.00	39.11	39.24	
q1	19.37	19.50	19.63	

- DIMENSIONING AND TOLERANCING PER ASME Y14.5M. 2018. CONTROLLING DIMENSION: MILLIMETER
- 2. CONTROLLING DIMELATION. M 3. HIROSE 12 PIN CONNECTOR 4. USB 3.0 Micro−B 5. M3X0.5 DEPTH ▼ 8.5.

- 1/4-20 UNC DEPTH ▼ 5.08 IMAGING SENSOR PLANE

DOCUMENT NUMBER:	98AON65112H	Electronic versions are uncontrolled except when accessed directly from Printed versions are uncontrolled except when stamped "CONTROLLED of the control of	
DESCRIPTION:	CMOD 90.89x61.00x61.00		PAGE 1 OF 1

onsemi and ONSEMi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, ONSEMI., and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems. or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

 $\textbf{Technical Library:} \ \underline{www.onsemi.com/design/resources/technical-documentation}$ 

onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at

www.onsemi.com/support/sales