



Acuros[®] CQD[®] 1920 GigE SWIR Camera

Acuros® CQD® cameras are the highest pixel resolution SWIR cameras sold commercially, enabling users to see features with the finest details. Our novel CQD sensors deliver full visible-to-SWIR band response, achieving lower costs per megapixel compared to InGaAs SWIR cameras. The Acuros CQD 1920 SWIR camera is designed with an integrated, multi-purpose 1920x1080 TEC Cooled CQD sensor, resulting in low noise and highly stable performance. Acuros cameras have up to a 10db higher SNR that competitive 5µm pixel InGaAs cameras.

Specifications:

Electro-Optical Specifications:	
Sensor	Acuros® CQD® sensor
Temperature stabilization	Single-stage thermo-electric cooler
Sensor array format	1920 x 1080
Resolution	2.07 megapixels
Spectral band	400 nm - 1700 nm
Array size	28.8 mm x 16.2 mm, 33 mm diagonal
Pixel pitch	15 μm x 15μm
Max frame rate at full resolution	58 fps (8 bit), 27fps (10, 12, 14 bit)
Pixel operability	99.9% typical, 99.75% min
Bit depth	8, 10, 12, 14 bit selectable
Integration type	Snapshot global shutter
Trigger	External TTL
Integration time	10 μsec to 4 sec
Dynamic range	70 dB typical
Windowing & windowing frame rate	Array centered. Scales inversely to window size
Laser beam fringeless operation	No (See Acuros Laser Series Cameras)
Binning arrays	2 x 2, 4 x 4
Non-uniformity correction	2-point non-uniformity correction
Temporal dark noise	65e ⁻ typical (high gain)
Quantum efficiency	See typical QE curve.

Features:

- Full HD resolution
- TEC cooling
- Low noise
- Fast frame rate
- Visible-SWIR
- GigE Vision
- High value

Applications:

- Machine vision
- Silicon inspection
- Automotive
- Fill-level
- Surveillance
- Hyperspectral
- Chemical sensors
- Agricultural
- Medical imaging
- Thermography

High Definition. SWIR Vision.

Specifications:

Environmental & power specifications, typical performance

Operating case temperature -20 °C to +55 °C

Power consumption 6.5 - 12 W depending on TEC settings

Power supply voltage 6-16 VDC. POE not supported.

Regulatory compliance CE mark

Mechanical specifications

Dimensions excluding lens 6.1 x 6.1 x 13.2 cm (F-mount) or 6.1 x 6.1 x 10.3 cm (M-42)

Weight excluding lens 594g with F-mount, 508g with M-42 mount

Lens mounts F-Mount, M42 (C-Mount flange-back distance)

Power connector Hirose 12-pin, HR10A-10R-12PB (71)

Trigger connector BNC

Software and user interface

Software development kit Windows GUI & Pleora eBUS SDK (Linux, Windows, MacOS)

GenlCam compliance Yes

Interface GigE Vision

Export compliance

US export designation EAR-99. No license required for lawful export

Ordering

Part numbers 1920: Acuros-1920-GigE-001



C-mount, F-mount, and M-42 Lens Mounts



GigE Vision Interface

Acuros CQD SWIR camera images


a.




b.




c




d





- a. Acuros 640: imaging through maritime rain event
- b. Acuros 640: imaging through pharmaceutical vial labels
- c. Acuros 1280: alignment mark in bonded wafers
- d. Acuros 1920: mag image of semiconductor chip edge





Contact Us:

For technical, pricing, and sales information, or to learn more about Acuros cameras or CQD sensor technology, please contact us at:

sales@swirvisionsystems.com

+1 919.248.0032





